

O FIT KIT

A multi-purpose stripping agent.



Product Details

This easily portable metric O-Ring splicing kit, enables rapid on the spot production of O-Rings which are ideal for emergency repairs or routine maintenance.

Kit Contents

The kit contains 14 x 2 metre packs of the most popular sizes of nitrile rubber cord, including: 1.78mm, 2mm, 2.4mm, 2.62mm, 3mm, 3.53mm, 4mm, 4.5mm, 5mm, 5.33mm, 5.7mm, 6mm, 7mm, 8mm.

Also included: cyanoacrylate adhesive, splicing jig, safety knife and a measuring tape.

Features and Benefits

- Both adhesive and cord are able to withstand temperatures ranging between minus 20 degrees C and plus 100 degrees C.
- Ideal for all workshops, on-site service engineers and service vehicles.
- Reduces downtime.
- Range of sizes.
- Strong storage box.

Making an O-Ring

Establish the length and size of the required cord. Use the knife and cutting block to cut the cord. Make sure that the cut is smooth and clean of oil grease and dust. Spread a thin layer of adhesive on one of the ends and using the ridge of the cutting block – unite the two ends. Holding the ends in the ridge, press firmly together for 20 to 30 seconds. Then leave to dry for 2 to 3 minutes.

Inspect the completed O-Ring which should now be ready for us

IMG Distributors Riverside Ind. Estate, Fazeley, Tamworth, Staffordshire B78 3RW.

The IM Group utilizes a process of continuous product improvement for all of our products. While the IM Group strictly adhere to our products specifications, we routinely implement product improvements. Therefore, please contact us for our most current product specifications. The IM Group warrants the quality of this product when used according to directions. Apply protective coatings per Company Standards. User shall determine suitability of product for use and assumes all risk. The seller will not accept liability for more than product replacement.